


## **MOUNTING INSTRUCTIONS**

А

INSTALL MOUNTING BOLTS CAPABLE OF SUPPORTING 144LB [65.2KG] DO NOT MOUNT IN DIRECT SUNLIGHT OR TEMPERATURES GREATER THAN 40C OR BELOW 5C ALL DIMENSIONS ARE IN INCHES [MILLIMETERS] 12 [305] CLEARANCES RECOMMENDED ON TOP, BOTTOM, LEFT AND RIGHT OF INSTRUMENT FRONT DOOR SHOULD HAVE ADEQUATE CLEARANCE TO SWING OPEN GREATER THAN 90 DEGREES INSTRUMENT MAY BE DIRECTLY BOLTED TO A WALL; ADEQUATE CLEARANCE IS PROVIDED BY SQUARE TUBING



INFORMATION CONTAINED HEREIN IS THE PROPERTY OF SIEVERS®, IS CONFIDENTIAL, IS NOT TO BE REPRODUCED, AND IS TO BE RETURNED UPON DEMAND.	Sievers® Analytical Instruments				
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES	6060 Spine Road Boulder, CO 80301 T(303) 444-2009 F(303) 444-9543 TITLE: M500, SUPER IOS, INSTALLATION DWG				
TOLERANCES ARE: .X ± .1 .XX ± .02 .XXX ± .005 ANGLES ± 1° FINISH 63 RMS					
	SCALE: 1:2				SHEET: 1 OF 1
GD&T PER ANSI/ASME Y14.5M-1994 DO NOT SCALE DRAWING	<sup>SIZE:</sup> D	Drawn Darren Smith	date 1/13/2021	PART NUMBER DIN 78430-01	REV A
	ĺ		Н	,	